


## External Central Loosetube Optical Cable – LSOH Sheath

IEC 60794-3-11

ACMA - AS/CA S008

### Cable Design



- Drawing not to scale -

- **Central loose tube construction**
- **Tube:** Thermoplastic material, containing up to 6 optical fibres filled with a low viscosity, thixotropic, non-melting gel fully compatible with fibre coating and tube material
- **Peripheral strength members:** Water swellable aramid yarns
- **Longitudinal water tightness:** Water swellable elements (dry-core technology)
- **Sheath:** UV stabilised zero halogen flame retardant low smoke and fume thermoplastic in compliance with AS 1049.

This loose tube dielectric optical cable is designed for indoor and outdoor installations in ducts by pulling, jetting or floating techniques. This cable is suitable for applications where low smoke generation, low toxicity and low acidic fumes under fire conditions are expected, such as tunnels and confined environments.

### Technical data

Number of Fibres	2 to 6			
Number of elements	1			
Tube diameter	mm	2.4		
Cable nominal diameter	mm	6.0		
Cable nominal weight	kg/km	32		
Max. installation tension	kN	1.0		
Max. crush resistance	kN/100 mm	2.0 (Short term) / 1.0 (Long term)		
Min. bending radius	mm	At full load	150	
		At no load	80	
Temperature range	°C	Installation -0 -> +50	Transport & Storage -20 -> +70	Operation -10 -> +70

### Optical Characteristics

See the attached cabled optical fibre data sheet.

### Identification

#### Fibre Colours


No.	1	2	3	4	5	6
Colour	blue	orange	green	brown	grey	white

#### Sheath Colour:

The outer sheath colour is light black.

**Sheath Marking:**

The outer sheath is marked in 1 meter intervals as follows:

PRYSMIAN DW SM@RTCORE LS LITE Part Number  N10514 T/N #### MM/YY MADE IN AUSTRALIA \*\*\*\*\*

**Main mechanical characteristics**

Parameter	Test method	Test conditions	Acceptance criteria*
Tensile strength	IEC 60794-1-2-E1	Load: As per cable maximum tensile strength in table above.	After 30 minutes the maximum strain on the fibre should not exceed 0.6% and no attenuation increase greater than 0.1 dB occurs
Crush	IEC 60794-1-2-E3	Short time: 10 min Long time: 120 min Load: As per maximum crush resistance in table above Number of positions: 3 adjacent sections (ensuring one over tube and one over lay reversal)	No damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs
Impact	IEC 60794-1-2-E4	Weight: 1.5 kg Height: 1.0 m Anvil radius: 12.5 mm Impacts: 1	After 5 minutes no fibre breaks, no damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs
Torsion	IEC 60794-1-2-E7	Sample length: 1 m Tension: As per table 1 of specification Rotation: a) 180° clockwise, b) return to starting position c) 180° anticlockwise d) return to starting position. Four movements constitute one cycle). Complete 10 cycles (a to d) in one minute maximum	During the final tenth cycle at a), c) and after completion (no rotation) check transmitting fibres. No fibre breaks, no damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs
Bend	IEC 60794-1-2-E11	Mandrel diameter: 160 mm Bend: 360° (1turn)	No attenuation increase greater than 0.1 dB occurs
Bend under tension	Concurrent to tensile test IEC 60794-1-2-E18	Mandrel diameter: 300 mm Bend: 360° (1turn)	After 1minute no fibre breaks, no damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs from no load to full load
Temperature cycling	IEC 60794-1-2-F1	Sample length: 1000 m (minimum) Temperature range: From - 10 °C to +70 °C	There should be no average attenuation increase at the temperature extremes when compared to the attenuation at ambient temperature. No individual fibre should measure an attenuation greater than 0.15 dB/km
Water penetration	IEC 60794-1-2-F5B	Sample length=3m, Water height=1m	No water leakage after 24 hour

\* All optical measurements for singlemode fibres performed at 1550 nm.

**Logistic**

**Packing:**

New non-returnable timber or plastic drums

**Delivery Lengths:**

Standard delivery length: 4 km with a tolerance of - 1% / + 3%

Maximum delivery length: 10 km with a tolerance of - 1% / + 3%

© PrysmianGroup 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup.