

Properties of cabled Bend-insensitive Multimode 50µm fibre

MaxCap-BB-OM3 Multimode Fibre

General and application

Prysmian MaxCap BendBright® OM3, laser-optimised, bend-insensitive, graded-index multimode fibres are designed for transmission speeds of 10 Gb/s and beyond. It is suitable for systems operating at 850 nm and 1300 nm wavelengths. MaxCap BendBright® OM3 fibres incorporate BendBright® technology to deliver enhanced macro-bending performance.

Standards and Norms

IEC 60793-2-10: type A1a.2	ISO / IEC 11801 Category OM3	ITU G.651.1
----------------------------	------------------------------	-------------

Attenuation & Optical properties

Attribute	Measurement method	Units	Limits
Attenuation @ 850 nm	IEC 60793-1-40	dB/km	≤ 2.5
Attenuation @ 1300 nm		dB/km	≤ 0.7
Point discontinuity @ 850 nm & 1300 nm		dB/km	≤ 0.1
Numerical aperture	IEC 60793-1-43	-	0.200 ± 0.015

Bandwidth

Attribute	Measurement method	Units	Limits
Overfilled launch modal bandwidth (OFL) @ 850 nm	IEC 60793-1-41	MHz.km	≥ 1500
Overfilled launch modal bandwidth (OFL) @ 1300 nm		MHz.km	≥ 500
Effective modal bandwidth (EMB) @ 850 nm	IEC 60793-1-49	MHz.km	≥ 2000

Group index of refraction

Attribute	Measurement method	Units	Limits
Typical group index of refraction @ 850 nm	IEC 60793-1-22	-	1.482
Typical group index of refraction @ 1300 nm		-	1.477

Geometrical properties

Attribute	Measurement method	Units	Limits
Core diameter	IEC 60793-1-20	µm	50 ± 2.5
Core non-circularity		%	≤ 5
Cladding diameter		µm	125.0 ± 1.0
Cladding non-circularity		%	≤ 1.0
Core-cladding concentricity error	IEC 60793-1-21	µm	≤ 1.5
Primary coating diameter		µm	245 ± 10
Primary coating non-circularity		%	≤ 5
Primary coating-cladding concentricity error		µm	≤ 10

Bending Loss

Attribute	Measurement method	Units	Limits
2 turns on a R= 7.5 mm mandrel @ 850 nm	IEC 60793-1-40	dB	≤ 0.2
2 turns on a R= 7.5 mm mandrel @ 1300 nm		dB	≤ 0.5
2 turns on a R= 15 mm mandrel @ 850 nm		dB	≤ 0.1
2 turns on a R= 15 mm mandrel @ 1300 nm		dB	≤ 0.3

Mechanical properties

<u>Attribute</u>	<u>Measurement method</u>	<u>Units</u>	<u>Limits</u>
Proof stress level	IEC 60793-1-30	GPa	≥ 0.7 ($\approx 1\%$)
Average strip force (F_{ave})	IEC 60793-1-32	N	$1.0 \leq F_{ave} \leq 3.0$
Peak strip force (F_{peak})		N	$1.3 \leq F_{peak} \leq 8.9$

© PrysmianGroup 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup.