


MEDIUM VOLTAGE CABLES
Copper 19/33 kV – Three core light duty screened armoured

Application

Electricity distribution or sub-transmission networks cable typically used as primary supply to Commercial, Industrial and urban residential networks. Suitable for low fault level or fast fault clearing cable systems.

Approvals

Approved by all major power Utilities and industrial customers in Australia.

Behaviour in flame and fire:

PVC or LSOH outer sheath exceeds the requirements of IEC 60332-1.

Temperature range

Minimum installation temperature: 0 °C
 Maximum operating temperature: +90 °C
 Minimum operating temperature: -25 °C

Minimum bending radius

Installed cables: 12D (PVC only)
 15D (HDPE)
 During installation: 18D (PVC only)
 25D (HDPE)

Resistance to

Chemical exposure: Accidental
 Mechanical impact: Heavy (Armoured)
 Water exposure: XLPE – Spray
 EPR – Immersion/Temporary coverage
 Solar radiation and weather exposure: Suitable for direct exposure.

Cable design
Conductor:

Plain circular compacted copper

Conductor screen:

Extruded semi-conductive compound, bonded to the insulation and applied in the same operations as the insulation.

Insulation:

Cross Linked Polyethylene (XLPE) – standard
 Ethylene Propylene Rubber (EPR) – alternative

Insulation screen:

Extruded, semi-conductive compound

Metallic screen:

Plain annealed copper wire: nominal 3kA for 1 second.
 See table next page.

Armouring:

Galvanised steel wires

Sheath:

Black 5V-90 polyvinyl chloride (PVC) – standard
 Orange 5V-90 PVC inner plus black high density polyethylene (HDPE) outer – alternative
 Low smoke zero halogen (LSOH) – alternative

Installation conditions

In free air
 In duct
 In trench
 In ground

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.



MEDIUM VOLTAGE CABLES

Physical & Electrical Characteristics

Copper 19/33 kV – Three core light duty screened armoured									
Product code: 3CCUX33LDA									
Nominal conductor area mm ²	50	70	95	120	150				
Nominal conductor diameter mm	8.2	9.8	11.5	12.9	14.3				
Nominal insulation thickness mm	8.0	8.0	8.0	8.0	8.0				
Approx cable diameter mm	79.9	84.1	88.0	91.4	94.8				
Approx mass kg/100m	920	1040	1160	1280	1400				
Max pulling tension on conductors kN	11	15	20	25	25				
Max pulling tension on stocking grip kN	11	15	20	25	25				
Max pulling tension on amour wires kN	25	25	25	25	25				
Min bending radius* during installation mm	1440	1510	1580	1640	1710				
Min bending radius* set in position mm	960	1010	1060	1100	1140				
Max conductor resistance, dc @ 20°C Ohm/km	0.387	0.268	0.193	0.153	0.124				
Conductor resistance, ac @ 90°C & 50 Hz Ohm/km	0.494	0.342	0.247	0.196	0.159				
Inductance mH/km	0.457	0.422	0.401	0.384	0.371				
Inductive reactance, @ 50Hz Ohm/km	0.143	0.133	0.126	0.121	0.117				
Zero seq. impedance @ 20°C & 50 Hz Ohm/km	2.32+ j0.0978	2.09+ j0.0871	1.92+ j0.0805	1.79+ j0.0752	1.69+ j0.0714				
Capacitance, phase to earth µF/km	0.140	0.155	0.171	0.184	0.197				
Min insulation resistance @ 20°C MOhm.km	18,000	16,000	15,000	14,000	13,000				
Electric stress at conductor screen kV/mm	4.07	3.85	3.67	3.55	3.46				
Charging current @ rated voltage & 50 Hz A/phase/km	0.834	0.927	1.02	1.10	1.17				
Short circuit rating	Phase conductor kA, 1 sec	7.2	10.0	13.6	17.2	21.5			
	Metallic screen kA, 1 sec	4.3	4.6	4.8	5.1	5.3			
Continuous current rating	In ground, direct buried A	190	235	280	320	365			
	In ground, in singleway ducts A	170	210	245	280	310			
	In free air, unenclosed & spaced from wall A	195	245	295	340	390			

The cables described are designed to be used for the supply of electrical energy in fixed applications up to the rated voltages at a nominal power frequency between 49Hz and 61Hz. All values are for XLPE cables only. *Increased radius required for HDPE and nylon incorporating designs.