

Surf's up!

FLEXTUBE[®] – a new wave of cables from Prysmian.



A brand of the

Prysmian
Group



Introducing *FLEXTUBE*[®]

FLEXTUBE[®] is an optical micro-module which can be built into many different designs of internal or external cables for extensive and widespread application.

The *FLEXTUBE*[®] micromodule is made of a soft, flexible material which makes it easy to use, especially when it is being prepared for end termination or mid-span breakout.






Easy installation and reduced costs

More dense and quicker to prepare and install, the Prysmian range of *FLEXTUBE*[®] cables offers many advantages compared with using standard loose tube optical cables. The key benefits of denser design and easier handling mean you make major savings in terms of time and cost – and the larger the project, the greater the savings.

What does it deliver to you?

- Reduced installation time.
 - Easier handling, particularly in fibre distribution and termination units.
 - Fast access to fibres; easy to remove the module material with no tools required.
 - Small quantity of grease, minimising clean-up time.
 - Avoid the risk of tube kinking (potentially causing attenuation increments or fibre breakage).
 - Simple mid-span breakout enabling single module extraction to aid distribution.
 - Available with Low-Smoke Halogen-Free Fire Retardant (HFFR) sheath compound for indoor applications.
 - Most *FLEXTUBE*[®] cables contain Prysmian Group's *BENDBRIGHT*^{XS} bend insensitive G.657.A2 fibres. In regular 250µm format or even denser 200µm versions, this enables the Flextubes to be wound around tight radii without signal loss. This supports the reduction in size of connectivity units, saving space and providing improved aesthetics.
- 



The *FLEXTUBE*[®] family of optical cables from Prysmian

The *FLEXTUBE*[®] family of optical micromodule designs was introduced by the Prysmian Group in order to provide even better performance than standard loose tube cables.

While loose tube products are still used extensively around the world and remain the most prevalent technology for cable designs (and produced globally in very high volumes by Prysmian Group) the *FLEXTUBE*[®] solution is able to create real benefits for operators, installers and other users through the key advantages of easy fibre access and breakout, avoiding attenuation risks through tube kinking, and providing much better thermal stability especially when tightly wound in joints. These benefits are achieved across the entire range of *FLEXTUBE*[®] designs.

One of the attractions of the *FLEXTUBE*[®] solution is its ability to address the full range of application areas with options that reflect customers' wants and needs.

- The optical micromodule itself is available with a single fibre within each unit up to 24-fibre packages (1, 2, 4, 6, 8, 12 and 24).
- Standard duct cables are available up to 864-fibre: there are two building-block options to cover the bulk of normal fibre counts, one for up to 288-fibre and another for those above (to 864-fibre). Higher fibre counts are available as customised solutions.
- Modified and improved designs that address customer demand for high density solutions.
- Cable designs for all application areas.



The range has expanded from the standard portfolio of *FLEXTUBE*[®] cables






The *FLEXTUBE*[®] family of optical micromodule designs has evolved over the years as our customers want to put more and more fibres into the duct space that they have available.


- **Mini *FLEXTUBE*[®] cables:** designed for μ duct installation, the material layers around the *FLEXTUBE*[®] microbundles are improved in these design options.
- **Micro *FLEXTUBE*[®] cables:** these cables are further enhanced by optimising the *FLEXTUBE*[®] module itself including new materials together with optimisation of cable designs.
- **Nano *FLEXTUBE*[®] cables:** the ultimate density solution, where the coating diameter of the fibre is reduced from 250 μ m to 200 μ m.

The effect of these improvements can be seen below, with the example of an 864-fibre *FLEXTUBE*[®] cable showing how the technology has assisted in reducing cable diameters.


42 mm Calibrated ID




22.2 mm
Standard



19.2 mm
Mini



17.0 mm
Micro



15.2 mm
Nano

When size matters, the extensive *FLEXTUBE*[®] family has the answers

If you want to optimise the fibre density of your network, you can move within the *FLEXTUBE*[®] duct/ μ duct family of optical micromodule designs from left to right in the earlier diagram and table below. Here, the external dimensions of the cable will reduce, as well as the net weight.

Depending upon the customer's (operator's) priorities, network design philosophy and topology, these issues may be highly beneficial or of little consequence; e.g. using blown installation practices will demand a significantly lower tensile strength requirement from the cable design.

Utilising the nano technology option in the *FLEXTUBE*[®] family, which incorporates 200 μ m *BENDBRIGHT*^{XS} G.657.A2 fibres, means that 72 fibres can be provided inside a 6mm cable and 864 fibres inside a 15.2mm cable with knock-on effects on microduct dimensions too. **This represents a record 4.8 fibres per mm².**



	Standard	Mini	Micro	Nano
Diameter (mm)	22.2	19.2	17.0	15.2
Design example (864f)				
Cable cross-section (mm ²)	387 (reference)	290 (-25%)	227 (-41%)	181 (-53%)
Fibre density in cable (fibres/mm ²)	2.2	3.0	3.8	4.8 RECORD
Fibre coating diameter (μ m)	250	250	250	200
Duct capacity (42 mm calibrated ID)	Reference			
Duct capacity vs. occupied space	864f /387 mm ² (reference)	1728f /579 mm ² (x2/+50%)	2592f /681 mm ² (x3/+76%)	3456f /726 mm ² (x4/+88%)

The *FLEXTUBE*[®] families are available in fibre counts up to 864. Higher fibre counts are available as customised solutions. The effects of the state-of-the-art density of *FLEXTUBE*[®] families are significant, as can be seen from the table above where the downward trend in overall cable dimensions means that 4x864-fibre nano *FLEXTUBE*[®] cables can now be installed in a calibrated 42 mm ID duct (a total of 3456 fibres), doubling the capacity compared to two years ago and quadrupling compared to historical reference.



Where to use *FLEXTUBE*[®] optical cables from Prysmian

FLEXTUBE[®] optical micromodule designs are available for the most extensive range of applications, throughout internal and external networks, whether traditional duct, micro-duct or direct buried networks or the most innovative solutions using new forms of rights-of-way.

Almost every application benefits from *FLEXTUBE*[®], including high value-add solutions deployed in crowded ducts and microducts, premises distribution, risers, sewer rights-of-way and aerial.

Other applications include:

- Direct buried
- Rodent resistant
- Gunshot resistant
- Façade
- Indoor and outdoor
- Hybrid
- Underwater
- Tunnel


How *FLEXTUBE*[®] goes beyond Loose Tube

FLEXTUBE[®] offers significant improvements over regular loose tube technology, delivering higher performance and operational savings for critical aspects of cable deployments. Three tests demonstrate these advantages clearly.


Kink

The *FLEXTUBE*[®] construction is immune to kinking, which is a key operational advantage over loose tube, which suffers from kinking at small bend diameters.

Loose Tube




FLEXTUBE[®]



Access to the fibres


Reduced preparation time for end access (approximately 40%) and reduced fibre access and coiling time for mid-span access (approximately 50%).



Extreme express module performance

When coiling inside a joint closure a *FLEXTUBE*® is extremely stable in temperature versus time (~0.2% variation), allowing operators to future-proof and secure their network against environmental conditions and maintenance tasks for decades.

This high level of attenuation stability can be considered state-of-the-art cable technology.





A global solution – now also manufactured in Sydney, Australia.

Around 40 countries have already benefited from the capabilities of *FLEXTUBE*[®] technology.

That includes broad adoption across Europe, significant deployments in Africa and the commencement of significant new builds in Latin America and Oceania.

Micromodule's versatility makes it the technology of choice throughout the network, spanning in-building solutions (risers, *VERTICASA*^{XS}), scalable FTTx and access (retracting systems), up to full end-to-end infrastructures in significant deployment cases.

The advantages of our solution can be leveraged in a wide variety of environments, taking in France, Germany, Spain, Portugal, UK, Benelux and several Eastern European countries among others, as well as Australia in the APAC region.

Linking the future

Prysmian Australia Pty Ltd

1 Heathcote Road, Liverpool 2170 NSW, Australia
Ph: 1300 300 304 Fx: 1300 300 307
E-mail: sales.au@prysmiangroup.com

www.prysmiancable.com.au

Prysmian New Zealand Ltd

30 Binsted Road, New Lynn 0600 Auckland, New Zealand
Ph: (09) 827 3109 Toll Free: 0800 492 225
E-mail: sales.nz@prysmiangroup.com

www.prysmiancable.co.nz



A brand of the
Prysmian
Group